

**Timken Multi-Use Lithium Grease EP2
Lubricating Grease**

Part Numbers

| | |
|--------|-------------------------|
| GR237C | 400 g (14 oz) cartridge |
| GR237T | 454 g (1 lb) tub |
| GR237F | 1 kg (2.2 lb) tub |
| GR237G | 5 kg (11 lb) pail |
| GR237P | 16 kg (35.3 lb) pail |
| GR237K | 55 kg (121.3 lb) keg |
| GR237D | 180 kg (400 lb) drum |

PRODUCT DESCRIPTION:

Timken Multi-Use Lithium EP2 grease is a lithium soap thickened grease containing a rust and oxidation inhibitor and EP additive. Timken Multi-Use Lithium EP2 provides good service life in a variety of bearing applications. Typical properties are listed below.

TYPICAL PHYSICAL PROPERTIES

| | |
|--|-------------------|
| Color | Amber |
| NLGI Grade | #2 |
| Thickener Type | Lithium |
| Penetration, D 217, worked 60 | 265-295 |
| Worked 100,000 pts change | 50 max |
| Dropping Point, °F, D 2265, | 350 min |
| Oil Separation, D 1742 % loss | 10 max |
| Corrosion Prevention, D 1743, | Pass |
| Copper Corrosion, D 4048, typical | 1b |
| Oxidation Stability, D 942, psi loss, 100 hrs | 5 max |
| Four-Ball Wear, ASTM D 2266, 40 kg, 1200 RPM, 75° C, Scar mm | 0.45 Max. |
| Four-Ball EP, Weld Point, ASTM D 2596, kgf | 250 Min. |
| Timken OK Load, ASTM D 2509, Pounds | 40 |
| Base Fluid Properties | |
| Base Fluid Type | Petroleum/Mineral |
| Viscosity @ 40°C, cSt D 445 | 145.6 |
| @ 100°C, cSt D 445 | 11.15 |
| Pour Point °F (°C) | 0 (-18) |
| Flash Point °F (°C) | 400 (204) |

Date: Feb 13, 2020

Timken Multi-Use Lithium EP NLGI Grade 2